



## HCT digital depth gauge with Bluetooth, Measuring range: 150mm



### Order data

Order number	418743 150
GTIN	4062406629472
Item class	42A

### Description

#### Version:

Measured result is displayed in easy-to-read digits. The measuring faces are precision lapped. Bluetooth 5.0. Compatible with the optional HCT (Hoffmann Group Connected Tools) mobile app. Available free of charge for Android and iOS and the HCT Windows app. Can also be used via a Human Interface Device (HID).

#### Supplied with:

1 battery No. 081560 size CR2032.

### Technical description

Number of batteries contained	1
Reversible reading	0.01 mm
Bridge length	100 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Wireless application	HID (Human Interface Device)
Wireless application	HCT Mobile App
Wireless application	HCT Windows app
Interface	Bluetooth interface
Measuring range	0 - 150 mm

Cross-section measuring beam	16×4 mm
Series	HCT
Battery type	Button cell
Power supply	Battery-powered
Calibration	A1
Reversible reading	0.0005 in
Measurement deviation E MPE	± 0.03 mm
Standard	ISO 13385
Reversible reading	mm / inch
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Depth gauge

## Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

## Accessories

Screw for depth gauge holder	412236
------------------------------	--------