

HOLEX

HCT digital caliper with Bluetooth and rod type depth gauge, Measuring range: 150mm



Order data

Order number	412792 150
GTIN	4062406629465
Item class	42A

Description

Version:

Digital caliper with **Bluetooth 5.0**. Easy-to-read LCD display. Very long battery running time due to modern energy-efficient measurement system. Easy-grip surface. Measuring faces are precision lapped. Compatible with the optional HCT (Hoffmann Group Connected Tools) mobile app. Available free of charge for Android and iOS. Can also be used via a Human Interface Device (HID). Programmable automatic shut-down and programmable automatic reaching of SLEEP mode via the HCT app.

Supplied with:

1 battery No. 081560 size CR2032.

Technical description

Standard	ISO 13385
Measuring range	0 - 150 mm
Depth gauge available	yes
Jaw length	40 mm
Depth gauge	Ø 1.6
Article no of the battery / rechargeable battery fitted	081560 No. CR2032
Series	HCT
Battery type	Button cell

Power supply	Battery-powered
Scale divisions	0.01 mm
Reversible reading	mm / inch
Number of batteries contained	1
Wireless application	HCT Mobile App
Wireless application	HID (Human Interface Device)
Wireless application	HCT Windows app
Calibration	A1
Scale divisions	0.0005 in
Measurement deviation E MPE	± 0.03 mm
Interface	Bluetooth interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Screw for depth gauge holder	412236