

HOLEX**Flat pot magnet with keeper plate, AlNiCo, Ø: 38mm****Order data**

Order number	085944 38
GTIN	4045197372857
Item class	02A

Description**Version:**

- Flat magnet in a protective steel jacket.
- Magnet fixed from below via countersunk hole.
- Magnetic material temperature-resistant up to maximum °C (size 19 up to 100 °C).

Application:

Jigs and fixtures.

Technical description

Ø	38.1 mm
Attachment hole Ø	5.2 mm
Material of the surface	Steel
Height	10.35 mm
Nominal clamping force	130 N
maximum temperature resistance	550 °C
Material of the magnet core	AlNiCo
Type of product	Pot magnet

