

Garant**Boring bar stabiliser 7×D maxi, Type: 10R****Order data**

Order number	319469 10R
GTIN	4062406642464
Item class	31V

Description**Version:**

Base body of high-quality tool steel, surface and functional faces hardened.

Advantage:

Reduces oscillation and vibration when used with all types of boring bars.

Suitable for:

All popular boring bars.

Note:

To determine the right type of boring bar stabiliser, it is essential to perform a collision check using the Hoffmann e-Tool data from the eShop or via the ToolScout! We recommend a maximum overhang length of 3×D of the types of boring bar used.

Maximum overhang, stabiliser incl. boring bar 10×D.

Technical description

Radius R	1.2 mm
C	1 mm
Offset Z to the axis	14 mm
Overhang L ₁	70 mm
Shank Ø D ₂	32 mm
Overall length L ₂	129 mm
Shank length L _s	53 mm

Cutting direction	right-hand
Ø D ₃	40 mm
Clamping Ø D ₁	10 mm
Boring depth up to	7×D
Vibration	damped
Type of product	Boring bar stabiliser