

## Eye-wash, Shank size: 2



### Order data

Order number	984150 2
GTIN	662641922419
Item class	97S

### Description

#### Version:

**Wall-mounted** eye and face shower with **open stainless steel basin** for indoor use. Can also be used outdoors, provided there is no possibility of freezing or overheating. Two spray nozzles protected by dust caps which lift off when the eye shower is activated. Quantity control valve for an optimum amount of water. Tightly-woven filter sieves and separate jet regulators ensure a gently flowing jet of water. To ANSI standard.

### Technical description

Manufacturer's designation	STD-85G(D)
Installation situation	wall-mounted
Application range	Internal and external
Flow rate	12 l/min
Flow pressure (bar)	29.01 - 87.02 lbf/in
Flow pressure (bar)	2 - 6 bar
Type of product	Eye-wash

