

Emergency shower, Shank size: 2



Order data

| | |
|--------------|--------------|
| Order number | 984160 2 |
| GTIN | 662641922396 |
| Item class | 97S |

Description

Version:

Emergency shower combination for floor mounting with eye and face shower. Suitable for indoor use. With open stainless steel tray for improved corrosion resistance and long working life. Operation of the emergency shower using the hand lever. Use of eye/face shower using the pressure pad or foot pedal. To ANSI standard. With stainless steel pipework.

Technical description

| | |
|----------------------------|-----------------|
| Depth | 741 mm |
| Installation situation | floor-mounted |
| BSP connection thread | 1,1/4 in |
| Height | 2288 mm |
| Manufacturer's designation | EXP-18GS/85G(D) |
| Application range | Internal |
| Width | 350 mm |
| Emergency shower flow rate | 76 l/min |

| | |
|------------------------------------|------------------|
| Eye/face washing station flow rate | 12 l/min |
| Flow pressure (bar) | 2 - 6 bar |
| Flow pressure (bar) | 29 lbf/in |
| Type of product | Emergency shower |