



Magnetic clamp with 90° (fixed), Ferrite, Type: 973



Order data

| | |
|--------------|---------------|
| Order number | 085954 973 |
| GTIN | 2050000965517 |
| Item class | 08Q |

Description

Version:

Angular tolerance $\pm 0.05 / 100$ mm. With two additional pressure levers.

Application:

For clamping components at a fixed angle of 90° and for preparing welding and assembly operations.

Technical description

| | |
|--------------------------|------------|
| Nominal clamping force | 2000 N |
| Height | 300 mm |
| Length | 300 mm |
| Type | 973 |
| Angular adjustment range | 90 degrees |
| Width | 35 mm |
| Weight | 4.7 kg |

| | |
|-----------------------------|--------------------|
| Material of the magnet core | Ferrite |
| Type of product | Magnet with switch |