

## Deep pot magnet with toleranced dimensions, AlNiCo, Ø: 16mm



### Order data

Order number	085925 16
GTIN	2050000965128
Item class	08Q

### Description

#### Version:

- **Shielded bar magnet with magnetic core of AlNiCo.**
- **Fit tolerance on the external Ø h6.**
- **Temperature-resistant up to maximum 220 °C.**

#### Application:

For clamping, assembling, incorporation by pressing in, gluing or encapsulating.

### Technical description

maximum shortening dimension rear	5 mm
Ø	16 mm
Height	20 mm
Material of the surface	galvanised
maximum temperature resistance	220 °C
Nominal clamping force	15 N
Material of the magnet core	AlNiCo
Type of product	Cylindrical clamping magnet

