


Garant
Solid carbide router cutter compacting cut fine, Diamond, Ø h10 DC: 5mm

Order data

Order number	209512 5
GTIN	4045197509819
Item class	11Y

Description
Version:

High performance diamond-pattern cut for efficient roughing of fibre-reinforced composites.

Technical description

Cutting edge Ø D _c	5 mm
No. of teeth Z	2
Shank Ø D _s	5 mm
Overall length L	50 mm
Flute length L _c	16 mm
Balance quality with shank	G 2.5 with HA
Feed f for side milling in GRP CRP	0.21 mm/rev.
Corner chamfer angle	90 degrees
Coating	Diamond
Toothing grit designation	fine
Tool material	Solid carbide
Standard	Manufacturer's standard
Milling profile	staggered teeth
Tolerance nominal Ø	h10
Direction of infeed	horizontal, oblique and vertical

Cutting width a_e for milling operation	0.5×D for side milling
Shank	DIN 6535 HA with h6
Through-coolant	no
Colour ring	black
Shank tolerance	h6
Type of product	Router

User data

	Suitability	V_c	ISO code
PVDF GF20	suitable	200 m/min	N
POM GF25	suitable	190 m/min	N
PA 66 GF30	suitable	170 m/min	N
PEEK GF30	suitable	150 m/min	N
PTFE CF25	suitable	180 m/min	N
PEEK CF30	suitable	160 m/min	N
Hybrids	suitable		
GRP	Suitable	190 m/min	N
CRP	Suitable	190 m/min	N
wet maximum	suitable		
dry	Suitable		
Air	suitable		