

**HOLEX****Button magnet with keeper plate, AlNiCo, Ø: 19mm****Order data**

Order number	085946 19
GTIN	4045197372895
Item class	02A

**Description****Version:**

- Round magnet with split adhesion surface and bore.
- Magnetic material temperature-resistant up to maximum 550 °C.

**Application:**

- For use with dial gauges.
- Fixing of small metal objects.

**Technical description**

Nominal clamping force	19 N
Ø	19 mm
Height	12.7 mm
Attachment hole Ø	4.8 mm
maximum temperature resistance	550 °C
Material of the magnet core	AlNiCo
Type of product	Button magnet

