

Deep pot magnet with toleranced dimensions, AlNiCo, Ø: 20mm**Order data**

Order number	085925 20
GTIN	2050000964824
Item class	08Q

Description**Version:**

- **Shielded bar magnet with magnetic core of AlNiCo.**
- **Fit tolerance on the external Ø h6.**
- **Temperature-resistant up to maximum 220 °C.**

Application:

For clamping, assembling, incorporation by pressing in, gluing or encapsulating.

Technical description

maximum shortening dimension rear	6 mm
Material of the surface	galvanised
Nominal clamping force	35 N
maximum temperature resistance	220 °C
Height	25 mm
Ø	20 mm
Material of the magnet core	AlNiCo
Type of product	Cylindrical clamping magnet

