



Magnetic holder, AlNiCo, Type: 925



Order data

Order number	085956 925
GTIN	2050000965470
Item class	08Q

Description

Version:

Steplessly adjustable magnetic force. The clamp has **6 magnetic faces:**

3 flat and 3 "Vee-form", set at an angle of 120°.

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

Application:

For powerful, fixed support of flat and round components (pipe \varnothing up to 76 mm) in a variety of angular positions.

maximum nominal clamping force: 1000 N

Height: 140 mm

Length: 108 mm

Width: 108 mm

Weight: 5.7 kg

Technical description

Length	108 mm
Width	108 mm
Type	925

maximum nominal clamping force	1000 N
Height	140 mm
Weight	5.7 kg
Material of the magnet core	AlNiCo
Type of product	Magnetic holder