



Open ended spanner/ratchet ring spanner set, in a wallet reversible 15° offset, Number of keys: 10



Order data

Order number	614838 10
GTIN	4062406649852
Item class	62A

Description

Version:

With particularly free-running sturdy ratchet at each end – reversible for left and right hand tightening. The 2 ends have different widths across flats.

Extremely small working arc of 5°.

In a handy textile tool roll.

Material:

Chrome vanadium steel, matt chrome-plated.

Supplied with:

1 each spanner No. 614828 in sizes 8; 9; 10; 11; 13; 14; 16; 17; 18; 19.

Technical description

Number of keys	10
Ring setting	15 degrees
No. of teeth	72
Working arc	5 degrees
Material	Chromium vanadium steel
Surface	matt chrome-plated
Width across flats	metric

Ratchet reversible	yes
Type of product	Spanners

Accessories

Open ended spanner/ratchet ring spannerreversible 15° offset Width across flats 8 mm	614828 8
Open ended spanner/ratchet ring spannerreversible 15° offset Width across flats 9 mm	614828 9
Open ended spanner/ratchet ring spannerreversible 15° offset Width across flats 10 mm	614828 10
Open ended spanner/ratchet ring spannerreversible 15° offset Width across flats 11 mm	614828 11
Open ended spanner/ratchet ring spannerreversible 15° offset Width across flats 13 mm	614828 13
Open ended spanner/ratchet ring spannerreversible 15° offset Width across flats 14 mm	614828 14
Open ended spanner/ratchet ring spannerreversible 15° offset Width across flats 16 mm	614828 16
Open ended spanner/ratchet ring spannerreversible 15° offset Width across flats 17 mm	614828 17
Open ended spanner/ratchet ring spannerreversible 15° offset Width across flats 18 mm	614828 18
Open ended spanner/ratchet ring spannerreversible 15° offset Width across flats 19 mm	614828 19