

**Oscillating saw and mitre saw BITURBO Cordless, Type: GCM18216-0****Order data**

Order number	078232 GCM18216-0
GTIN	3165140898928
Item class	03B

Description**Version:**

Cordless pivoting saw and mitre saw.

- **Excellent cutting capacity with a large cutting depth of 70 mm.**
- **Best mobility thanks to its low weight and outstanding ergonomics.**
- **User interface for speed pre-selection.**
- **Tool-free saw blade change.**
- **Thanks to BITURBO technology comparable with saws with cables.**
- **Good mobility thanks to low weight.**

Supplied with:

Saw blade Ø 216 mm, hold-down clamp, SDS nut, GCY 42 Bluetooth module. Including saw blade and dust bag.

Technical description

maximum inclination angle left	45 degrees
maximum inclination angle right	0 degrees
Manufacturer's designation	GCM 18V-216
Mitre angle adjustment	yes
Height	630 mm

maximum mitre angle left	47 degrees
Type of rechargeable battery	Lithium-ion
Width	770 mm
Battery voltage	18 V
Weight	14.7 kg
Length	520 mm
suitable battery - supplier / battery type / voltage	Bosch 18 V
Saw blade Ø	216 mm
maximum mitre angle right	47 degrees
Number of rechargeable batteries contained	0
Power supply	Rechargeable battery-powered
maximum speed	4600 min ⁻¹
Packaging	cardboard
Type of product	Saw