

**Button magnet with keeper plate, AlNiCo, Ø: 25mm****Order data**

Order number	085946 25
GTIN	4045197372918
Item class	02A

Description**Version:**

- Round magnet with split adhesion surface and bore.
- Magnetic material temperature-resistant up to maximum 550 °C.

Application:

- For use with dial gauges.
- Fixing of small metal objects.

Technical description

Attachment hole Ø	4.8 mm
maximum temperature resistance	550 °C
Height	15.9 mm
Ø	25 mm
Nominal clamping force	34 N
Material of the magnet core	AlNiCo
Type of product	Button magnet

