

HEDI

Compressed air hose reel 1/4 inch, usable hose length: 20 m



Order data

Order number	080060 20
GTIN	4003644006632
Item class	08B

Description

Version:

Sheet steel industrial hose reel with ergonomic handle, high stability, turning handle and drum brake. Hose internal $\varnothing = 9$ mm; operating pressure maximum 12 bar.

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

maximum operating pressure: 12 bar

usable hose length: 20 m

Hose internal \varnothing : 9 mm

Technical description

Hose internal \varnothing	9 mm
Material of the housing	Sheet steel
maximum operating pressure	12 bar
usable hose length	20 m
Type of product	Hose reel

Accessories

Compressed air hose reel 1/4 inch without hose Type LEER

080065 LEER