

**Deep pot magnet with toleranced dimensions, AlNiCo, Ø: 25mm****Order data**

Order number	085925 25
GTIN	2050000964831
Item class	08Q

**Description****Version:**

- **Shielded bar magnet with magnetic core of AlNiCo.**
- **Fit tolerance on the external Ø h6.**
- **Temperature-resistant up to maximum 220 °C.**

**Application:**

For clamping, assembling, incorporation by pressing in, gluing or encapsulating.

**Technical description**

Material of the surface	galvanised
maximum temperature resistance	220 °C
Ø	25 mm
Height	30 mm
maximum shortening dimension rear	5 mm
Nominal clamping force	80 N
Material of the magnet core	AlNiCo
Type of product	Cylindrical clamping magnet

