

# uvex

Sandal, black/yellow uvex 1, S1, EU shoe size: 40



## Order data

Order number	092110 40
GTIN	4031101543062
Item class	04V

## Description

### Version:

Sporty, especially lightweight and flexible safety shoe. Suitable for wearers allergic to chromium. Width 11.

- **Micro-velour uppers.**
- **Distance Mesh lining material.**
- **100% metal-free uvex xenova® toecap.**
- **PU sole with TPU inserts with the best damping characteristics.**
- **Virtually seamless design to avoid pressure points.**
- **ESD security.**

Safety sandals with double hook and loop fastening and large ventilation openings.

### Standard:

EN ISO 20345:2011 S1 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

electrostatic characteristic: EGB/ESD

Protection class: S1

Material of protective toe-cap: Composite

Standard: Inlay type-tested according to DGUV regulation 191

## Technical description

Energy absorption in the heel area	yes
anti-static	yes

The entire shoe is waterproof	no
Closure	Hook and loop fastener
suitable for those with chrome allergy.	yes
against water penetration and water absorption	no
Size UK	6.5
Standard	Inlay type-tested according to DGUV regulation 191
Slip resistance	yes
Colour	black / yellow
oil- and petrol-resistant sole	no
profiled outer sole	yes
removable footbed	yes
Uppers material	Hydrophobic high-tech micro-velour
Material of outer sole	PU
EU shoe size	40
Shoe type	Sandals
Material inner lining	Distance Mesh lining material
Material of protective toe-cap	Composite
Size US	8.5
Protection class	S1
Series	uvex 1
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Type of product	Safety sandals