



Cordless nutrunner, right angle, Type: CLBA123



Order data

Order number	071142 CLBA123
GTIN	697099651499
Item class	03S

Description

Version:

The cordless Cleco® CellClutch™ assembly tools are smart yet simple to use, and bring programming functionality to the assembly line along with a classic counting function. Precision and repetition accuracy with a CMK value > 1.67 (at a tolerance of $\pm 10\%$ in conjunction with ISO 5393).

- **Easy to program: Program speeds and multi-stage screw tightening procedures to avoid errors and improve productivity.**
- **Tried-and-tested Cleco clutch: For reliability and a long service life in the production line.**
- **Operator status light: Colour display for screw tightening and batch counting status.**
- **Multi-colour LED: Work light for additional "OK/NOK" user feedback whilst also illuminating your workpiece.**
- **Programmable screwdriving strategies: Eliminate damage to the thread and errors when screwdriving thanks to programmable speeds and strategies.**
- **Uniform battery platform.**

Supplied with:

Without batteries and without charger.

Note:

You can find suitable batteries and chargers under No. 073827 size MB18; 073816 size MB18 and under No. 073840. A pre-setting device is necessary for setting the torque; these can be found from No. 654381.

Technical description

Length	452.4 mm
Power supply	Rechargeable battery-powered
Battery capacity	3 Ah
Tool arbor drive profile	Square
Tool arbor size	3/8 in
Speed range	65 - 650 min ⁻¹
Battery voltage	18 V
Height	76 mm
Number of rechargeable batteries contained	0
Weight without battery	1.46 kg
Torque range	3.3 - 12 Nm
Type of product	Screwdriver