



Cordless nutrunner, pistol, Type: CLBP04Q



Order data

Order number	071143 CLBP04Q
GTIN	697099651543
Item class	03S

Description

Version:

The cordless Cleco® CellClutch™ assembly tools are smart yet simple to use, and bring programming functionality to the assembly line along with a classic counting function. Precision and repetition accuracy with a CMK value > 1.67 (at a tolerance of ±10% in conjunction with ISO 5393).

- **Easy to program: Program speeds and multi-stage screw tightening procedures to avoid errors and improve productivity.**
- **Tried-and-tested Cleco clutch: For reliability and a long service life in the production line.**
- **Operator status light: Colour display for screw tightening and batch counting status.**
- **Multi-colour LED: Work light for additional "OK/NOK" user feedback whilst also illuminating your workpiece.**
- **Programmable screwdriving strategies: Eliminate damage to the thread and errors when screwdriving thanks to programmable speeds and strategies.**
- **Uniform battery platform.**

Supplied with:

Without batteries and without charger.

Note:

You can find suitable batteries and chargers under No. 073827 size MB18; 073816 size MB18 and under No. 073840. A pre-setting device is necessary for setting the torque; these can be found from No. 654381.

Technical description

Power supply	Rechargeable battery-powered
Toolholder	Quick-change chuck
Battery capacity	2 Ah
Height	209 mm
maximum speed	1770 min ⁻¹
Tool arbor size	1/4 in
Length	213.5 mm
maximum torque	4 Nm
Weight without battery	1.04 kg
Battery voltage	18 V
Torque range	1.1 - 4 Nm
Type of product	Screwdriver