

# uvex

## Shoe, black/yellow uvex 1, S2, EU shoe size: 37



### Order data

Order number	092115 37
GTIN	4031101534633
Item class	04V

### Description

#### Version:

Sporty, especially lightweight and flexible safety shoe. Suitable for wearers allergic to chromium. Width 11.

- **Micro-velour uppers.**
- **Distance Mesh lining material.**
- **100% metal-free uvex xenova® toecap.**
- **PU sole with TPU inserts with the best damping characteristics.**
- **Virtually seamless design to avoid pressure points.**
- **ESD security.**

Safety shoes with elastic laces and quick fastening.

#### Standard:

EN ISO 20345:2011 S2 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

electrostatic characteristic: EGB/ESD

Protection class: S2

Material of protective toe-cap: Composite

Standard: Inlay type-tested according to DGUV regulation 191

### Technical description

removable footbed	yes
Material of protective toe-cap	Composite

Energy absorption in the heel area	yes
Slip resistance	yes
Colour	black / yellow
Standard	Inlay type-tested according to DGUV regulation 191
profiled outer sole	yes
Uppers material	Hydrophobic high-tech micro-velour
Protection class	S2
EU shoe size	37
Material of outer sole	PU
anti-static	yes
Material inner lining	Distance Mesh lining material
Shoe type	Low shoe
oil- and petrol-resistant sole	yes
Series	uvex 1
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Type of product	Safety shoes