

**Strong magnet with keeper plate, AlNiCo, Overall height: 20mm****Order data**

Order number	085934 20
GTIN	4045197372543
Item class	02A

Description**Version:**

- **Strong, bridge-shaped magnet.**
- **With hole for fixing the magnet. (sizes 35 and 41 with 2 holes).**
- **Magnetic material temperature-resistant up to maximum 550 °C.**

Application:

For holding, lifting or sorting small iron parts or for installation in electrical relays, measuring instruments etc.

Technical description

Overall height	20 mm
maximum temperature resistance	550 °C
Nominal clamping force	45 N
Single-pole depth	8 mm
Single-pole width	20 mm
Material of the magnet core	AlNiCo
Type of product	Strong magnet

