

HOLEX**Button magnet with keeper plate, AlNiCo, Ø: 32mm****Order data**

Order number	085946 32
GTIN	4045197608604
Item class	02A

Description**Version:**

- Round magnet with split adhesion surface and bore.
- Magnetic material temperature-resistant up to maximum 550 °C.

Application:

- For use with dial gauges.
- Fixing of small metal objects.

Technical description

Ø	32 mm
Nominal clamping force	48 N
Attachment hole Ø	7.1 mm
Height	25.4 mm
maximum temperature resistance	550 °C
Material of the magnet core	AlNiCo
Type of product	Button magnet

