

**Pot magnet with keeper plate, AlNiCo, Ø: 21mm****Order data**

Order number	085940 21
GTIN	4045197372758
Item class	02A

Description**Version:**

- **Machining the steel jacket will not impair magnet performance.**
- **Magnetic force directed downwards as cased in an aluminium ring.**
- **Tapped hole in the magnet top face, for fastening.**
- **Magnetic material temperature-resistant up to maximum 220 °C.**

Application:

Incorporation in jigs, for holding or lifting.

Technical description

maximum temperature resistance	220 °C
Ø	21 mm
Height	19 mm
Nominal clamping force	40 N
Material of the surface	Steel
Tapped attachment hole in the magnet head	M6 mm

Material of the magnet core	AlNiCo
Type of product	Pot magnet