

Re-Bo**Metal circular saw blade, Ø×thickness: 68X1,6Mmm**

Order data

Order number	178860 68X1,6M
GTIN	4045197245601
Item class	17B

Description

Version:**Top quality German product**, hollow ground with precision tooth format.**Suitable for:****GF** and **AXX AiR**.

Technical description

Thickness	1.6 mm
Ø	68 mm
Bore Ø	16 mm
No. of teeth Z	64
Tool material	HSS E
Through-coolant	no
Type of product	Circular saw blade

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable	800 m/min	N
Alu > 10% Si	suitable	600 m/min	N
Steel < 500 N/mm ²	suitable	37 m/min	P
Steel < 750 N/mm ²	suitable	22 m/min	P
Steel < 900 N/mm ²	suitable	20 m/min	P
Steel < 1100 N/mm ²	suitable only under restricted conditions	15 m/min	P
INOX < 900 N/mm ²	suitable	11 m/min	M
INOX > 900 N/mm ²	suitable	11 m/min	M
Ti > 850 N/mm ²	suitable only under restricted conditions	15 m/min	S
GG(G)	suitable	27 m/min	K
CuZn	suitable	400 m/min	N
Uni	suitable		
wet maximum	suitable		
dry	suitable		
Air	suitable only under restricted conditions		