

Deep pot magnet with toleranced dimensions, AlNiCo, Ø: 40mm**Order data**

Order number	085925 40
GTIN	2050000965142
Item class	08Q

Description**Version:**

- **Shielded bar magnet with magnetic core of AlNiCo.**
- **Fit tolerance on the external Ø h6.**
- **Temperature-resistant up to maximum 220 °C.**

Application:

For clamping, assembling, incorporation by pressing in, gluing or encapsulating.

Technical description

Nominal clamping force	200 N
Material of the surface	galvanised
Height	45 mm
maximum temperature resistance	220 °C
maximum shortening dimension rear	5 mm
Ø	40 mm
Material of the magnet core	AlNiCo
Type of product	Cylindrical clamping magnet

