


Flat magnet with internal thread, Neodymium, Ø: 25mm



Order data

Order number	085924 25
GTIN	2050001737779
Item class	08Q

Description

Version:

- Temperature-resistant up to maximum 80 °C.
- Galvanised surface, magnetic core made of neodymium.
- Shielded flat magnet with 3 to 6 times the clamping force compared to hard ferrite magnets.

Application:

For clamping, assembling, incorporation by pressing in, gluing or encapsulating.

Note:

Screw-in hooks with external thread under No. 085921.

Technical description

Height with thread	14 mm
Nominal clamping force	200 N
Height	7 mm
Thread	M4 mm
Ø	25 mm
Weight	34 g
maximum temperature resistance	80 °C
Threaded socket	yes

Material of the surface	galvanised
Material of the magnet core	Neodymium
Type of product	Flat gripper magnet

Accessories

Screw-in hook set with external thread 10 pieces Thread M4	085921 M4
------------------------------------------------------------	-----------