

Flat magnet without thread, Neodymium, Ø: 20mm



Order data

Order number	085923 20
GTIN	2050001737687
Item class	08Q

Description

Version:

- Temperature-resistant up to maximum 80 °C.
- Galvanised surface, magnetic core made of neodymium.
- Shielded flat magnet with 3 to 6 times the clamping force compared to hard ferrite magnets.

Application:

For clamping, assembling, incorporation by pressing in, gluing or encapsulating.

Technical description

Ø	20 mm
Nominal clamping force	140 N
Material of the surface	galvanised
Weight	15 g
Height	6 mm
maximum temperature resistance	80 °C
Material of the magnet core	Neodymium
Type of product	Flat gripper magnet

