

Deep pot magnet with toleranced dimensions, AlNiCo, Ø: 50mm



Order data

Order number	085925 50
GTIN	2050000964848
Item class	08Q

Description

Version:

- **Shielded bar magnet with magnetic core of AlNiCo.**
- **Fit tolerance on the external Ø h6.**
- **Temperature-resistant up to maximum 220 °C.**

Application:

For clamping, assembling, incorporation by pressing in, gluing or encapsulating.

Technical description

Material of the surface	galvanised
maximum shortening dimension rear	2 mm
Nominal clamping force	350 N
Ø	50 mm
maximum temperature resistance	220 °C
Height	50 mm
Material of the magnet core	AlNiCo
Type of product	Cylindrical clamping magnet

