


## Flat magnet with internal thread, Neodymium, Ø: 32mm



### Order data

Order number	085924 32
GTIN	2050001737786
Item class	08Q

### Description

#### Version:

- Temperature-resistant up to maximum 80 °C.
- Galvanised surface, magnetic core made of neodymium.
- Shielded flat magnet with 3 to 6 times the clamping force compared to hard ferrite magnets.

#### Application:

For clamping, assembling, incorporation by pressing in, gluing or encapsulating.

#### Note:

Screw-in hooks with external thread under No. 085921.

### Technical description

Nominal clamping force	350 N
Threaded socket	yes
Material of the surface	galvanised
Weight	48 g
Ø	32 mm
Height with thread	15.5 mm
Thread	M5 mm
maximum temperature resistance	80 °C

Height	7 mm
Material of the magnet core	Neodymium
Type of product	Flat gripper magnet

---

## Accessories

Screw-in hook set with external thread 10 pieces Thread M5	085921 M5
--	-----------