

HOLEX**Flat pot magnet with keeper plate, AlNiCo, Ø: 19mm****Order data**

| | |
|--------------|---------------|
| Order number | 085944 19 |
| GTIN | 4045197372819 |
| Item class | 02A |

Description**Version:**

- Flat magnet in a protective steel jacket.
- Magnet fixed from below via countersunk hole.
- Magnetic material temperature-resistant up to maximum °C (size 19 up to 100 °C).

Application:

Jigs and fixtures.

Technical description

| | |
|--------------------------------|------------|
| Material of the surface | Steel |
| Height | 7.5 mm |
| maximum temperature resistance | 100 °C |
| Attachment hole Ø | 4.5 mm |
| Nominal clamping force | 30 N |
| Ø | 19 mm |
| Material of the magnet core | AlNiCo |
| Type of product | Pot magnet |

