



Adjustable magnetic clamp, Ferrite, Type: 952



Order data

Order number	085950 952
GTIN	2050000965449
Item class	08Q

Description

Version:

Jaws **adjustable from 25° to 280°**. Most common angles 90°, 60°, 45°, and 30° are marked for quick reference.

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

Application:

For precise holding of steel plates and pipes during welding and assembly operations.

Nominal clamping force: 200 N

Height: 200 mm

Length: 195 mm

Width: 11 mm

Weight: 0.49 kg

Technical description

Weight	0.49 kg
Length	195 mm
Nominal clamping force	200 N
Angular adjustment range	25 - 280 °
Width	11 mm
Type	952
Height	200 mm

Material of the magnet core	Ferrite
Type of product	Magnet with switch