



## Adjustable magnetic clamp, Ferrite, Type: 952



### Order data

Order number	085950 952
GTIN	2050000965449
Item class	08Q

### Description

**Version:**

Jaws **adjustable from 25° to 280°**. Most common angles 90°, 60°, 45°, and 30° are marked for quick reference.

**Application:**

For precise holding of steel plates and pipes during welding and assembly operations.

### Technical description

Weight	0.49 kg
Length	195 mm
Nominal clamping force	200 N
Angular adjustment range	25 - 280 degrees
Width	11 mm
Type	952
Height	200 mm
Material of the magnet core	Ferrite
Type of product	Magnet with switch