

Garant
GARANT Master Turn boring bar, steel spiral flutes, right-hand, Shank \varnothing / insert size: 10/11mm

Order data

Order number	260932 10/11
GTIN	4062406677244
Item class	21T

Technical description

Series	GARANT Master
ISO code toolholder	A10K STFCCR/L11
Overall length L	125 mm
Setting angle κ	90 degrees
Pack of insert screws	269028 7
Centre offset L_3	6.2 mm
Shank $\varnothing D_s$	10 mm
Head length L_1	22 mm
Clamping height L_2	9 mm
Insert size	11 mm
suitable indexable insert	TC.. 1102..
Minimum pre-drill $\varnothing D_{\min}$	12 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar