

**Garant**
**GARANT Master Turn boring bar, steel spiral flutes, right-hand, Shank  $\varnothing$  / insert size: 16/11mm**

**Order data**

Order number	260932 16/11
GTIN	4062406677268
Item class	21T

**Technical description**

Head length $L_1$	31 mm
Centre offset $L_3$	9.2 mm
Setting angle $\kappa$	90 degrees
Shank $\varnothing D_s$	16 mm
suitable indexable insert	TC.. 1102..
Overall length L	180 mm
Minimum pre-drill $\varnothing D_{min}$	18 mm
Insert size	11 mm
Pack of insert screws	269028 7
ISO code toolholder	A16Q STFCR/L11
Clamping height $L_2$	15 mm
Series	GARANT Master
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar