

**Garant**
**GARANT Master Turn boring bar, steel spiral flutes, right-hand, Shank  $\varnothing$  / insert size: 12/11mm**

**Order data**

Order number	260932 12/11
GTIN	4062406677251
Item class	21T

**Technical description**

Head length $L_1$	24.3 mm
Shank $\varnothing D_s$	12 mm
Pack of insert screws	269028 7
Overall length L	140 mm
Minimum pre-drill $\varnothing D_{\min}$	14 mm
suitable indexable insert	TC.. 1102..
Series	GARANT Master
Clamping height $L_2$	11 mm
Insert size	11 mm
ISO code toolholder	A12L STFCL/L11
Centre offset $L_3$	7.2 mm
Setting angle $\kappa$	90 degrees
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar