



Video endoscope without probe, Type: F1100



Order data

Order number	492923 F1100
GTIN	4062406684471
Item class	42L

Description

Version:

HOLEX video endoscope with large LCD display showing true-scale details, and comprehensive functions. The sun shade offers additional protection when in sunlight. The unit can be held steady using the two handles. The base unit is compatible with all HOLEX endoscope probes No. 492932 – 492944.

- **Base unit with 7 inch LCD display (image cut-out 6 inches).**
- **Zoom mode; 3 stages of digital zoom: 1.5×, 2× and 5×.**
- **Images and video recordings can be saved.**
- **USB and AV output. The integral USB and AV outputs allow your images and videos to be transferred to a PC.**
- **Integral rechargeable Li-ion battery with 5 hour capacity.**
- **180° image rotation / reflection.**

Advantage:

- **Intuitive touch display with full screen display.**
- **Exceptionally robust and ideally suited for use outdoors.**
- **Very large image aperture of 6 inches.**
- **Image aperture with adapter can be divided for parallel display of 0° and 90° viewing when using a probe Ø 6 mm.**
- **Facility for adding comments by sound recording. The built-in microphone can be used during video operation for recording comments during the inspection. This eliminates the need for laborious writing and compilation of notes.**

- **Notes can be added for images.**
- **Comparison of saved images with live images.**
- **Selected settings can be clearly shown directly on the display.**

Function:

IP55: Protected against jets of water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Sturdy watertight and dust-tight transport case, SD memory card, power supply unit (AC 100 – 240 V / 50 – 60 Hz), USB data cable, AV cable, cleaning kit. **Without probe.**

Optional extras:

Endoscope probes No. 492932 – 492944.

IP Index of Protection: IP 55

Recording format: JPEG / AVI (30fps)

Display size: 7 in

Display resolution: 640×480 px

depth of focus when focussed: 16 – 60 mm

Operating temperature: 0 - 40 °C

Technical description

On/Off switch	yes
Recording format	JPEG / AVI (30fps)
Power supply	Mains-powered
Power supply	Rechargeable battery-powered
IP Index of Protection	IP 55
depth of focus when focussed	16 – 60 mm
Display size	7 in
Display resolution	640×480 px
Operating temperature	0 - 40 °C
Display	Touch screen
Type of product	Endoscope

Accessories

Lithium ion battery Type	492918
--------------------------	--------

