

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 8/05mm


Order data

Order number	261378 8/05
GTIN	4062406710736
Item class	21T

Technical description

suitable indexable insert	VC.. 0501..
Pack of insert screws	269028 26
Overall length L	80 mm
Minimum pre-drill $\varnothing D_{\min}$	8 mm
Centre offset L_3	3 mm
Head length L_1	15 mm
Clamping height L_2	7.5 mm
Setting angle κ	140 degrees
Insert size	5 mm
Shank $\varnothing D_s$	8 mm
ISO code toolholder	A08F SVOCR/L05
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

