

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 16/11mm

Order data

Order number	261378 16/11
GTIN	4062406710767
Item class	21T

Technical description

Shank $\varnothing D_s$	16 mm
Centre offset L_3	9 mm
Pack of insert screws	269028 7
Setting angle κ	140 degrees
Clamping height L_2	15 mm
Minimum pre-drill $\varnothing D_{min}$	22 mm
Insert size	11 mm
ISO code toolholder	A16M SVOCR/L11
Head length L_1	35 mm
suitable indexable insert	VC.. 1103..
Overall length L	150 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

