

Garant**Boring bar, steel, left-hand, Shank Ø / insert size: 12/07mm****Order data**

Order number	261379 12/07
GTIN	4062406710804
Item class	21T

Technical description

Minimum pre-drill Ø D _{min}	13 mm
Centre offset L ₃	6.5 mm
Setting angle κ	140 degrees
suitable indexable insert	VC.. 0702..
Clamping height L ₂	11 mm
ISO code toolholder	A12L SVOCR/L07
Head length L ₁	24 mm
Insert size	7 mm
Overall length L	140 mm
Shank Ø D _s	12 mm
Pack of insert screws	269028 27
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

