

**Garant**
**Boring bar, steel, right-hand, Shank  $\varnothing$  / insert size: 20/11 mm**

**Order data**

Order number	261378 20/11
GTIN	4062406710774
Item class	21T

**Technical description**

Clamping height $L_2$	19 mm
Insert size	11 mm
Centre offset $L_3$	11 mm
suitable indexable insert	VC.. 1103..
Shank $\varnothing D_s$	20 mm
Setting angle $\kappa$	140 degrees
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{min}$	24 mm
ISO code toolholder	A20Q SVOCR/L11
Head length $L_1$	40 mm
Overall length $L$	180 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

