

**Garant**
**Boring bar, steel, right-hand, Shank  $\varnothing$  / insert size: 10/07mm**

**Order data**

Order number	261378 10/07
GTIN	4062406710743
Item class	21T

**Technical description**

suitable indexable insert	VC.. 0702..
Clamping height $L_2$	9 mm
Insert size	7 mm
Centre offset $L_3$	5.5 mm
Overall length $L$	100 mm
Minimum pre-drill $\varnothing D_{\min}$	11 mm
Head length $L_1$	22 mm
Pack of insert screws	269028 27
ISO code toolholder	A10H SVOCR/L07
Shank $\varnothing D_s$	10 mm
Setting angle $\kappa$	140 degrees
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

