

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 20/11 mm

Order data

Order number	261379 20/11
GTIN	4062406710828
Item class	21T

Technical description

Pack of insert screws	269028 7
suitable indexable insert	VC.. 1103..
Shank Ø D _s	20 mm
Minimum pre-drill Ø D _{min}	24 mm
Setting angle κ	140 degrees
Clamping height L ₂	19 mm
Overall length L	180 mm
Centre offset L ₃	11 mm
Head length L ₁	40 mm
Insert size	11 mm
ISO code toolholder	A20Q SVOCR/L11
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

