

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 16/11 mm

Order data

Order number	261379 16/11
GTIN	4062406710811
Item class	21T

Technical description

Overall length L	150 mm
ISO code toolholder	A16M SVOCR/L11
Setting angle κ	140 degrees
suitable indexable insert	VC.. 1103..
Minimum pre-drill $\varnothing D_{\min}$	22 mm
Pack of insert screws	269028 7
Shank $\varnothing D_s$	16 mm
Insert size	11 mm
Centre offset L_3	9 mm
Clamping height L_2	15 mm
Head length L_1	35 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

