

Garant
Boring bar carbide, right-hand, Shank \varnothing / insert size: 10/07mm


Order data

Order number	261376 10/07
GTIN	4062406710842
Item class	21T

Technical description

ISO code toolholder	E10H SVOCR/L07
suitable indexable insert	VC.. 0702..
Clamping height L_2	9 mm
Pack of insert screws	269028 27
Minimum pre-drill $\varnothing D_{\min}$	11 mm
Overall length L	100 mm
Shank $\varnothing D_s$	10 mm
Insert size	7 mm
Setting angle κ	140 degrees
Centre offset L_3	5.5 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

