

Garant
Boring bar carbide, left-hand, Shank \varnothing / insert size: 10/07mm

Order data

Order number	261377 10/07
GTIN	4062406710866
Item class	21T

Technical description

suitable indexable insert	VC.. 0702..
Insert size	7 mm
Centre offset L_3	5.5 mm
Setting angle κ	140 degrees
Shank $\varnothing D_s$	10 mm
Pack of insert screws	269028 27
Clamping height L_2	9 mm
Minimum pre-drill $\varnothing D_{min}$	11 mm
Overall length L	100 mm
ISO code toolholder	E10H SVOCR/L07
Standard	Works standard
Application type	left-hand
Boring depth up to	8×D
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

