

Garant
Boring bar carbide, left-hand, Shank \varnothing / insert size: 8/05mm

Order data

| | |
|--------------|---------------|
| Order number | 261377 8/05 |
| GTIN | 4062406710859 |
| Item class | 21T |

Technical description

| | |
|---|-------------------------------|
| Centre offset L_3 | 3 mm |
| suitable indexable insert | VC.. 0501.. |
| Head length L_1 | 26 mm |
| Overall length L | 80 mm |
| Shank $\varnothing D_s$ | 8 mm |
| Minimum pre-drill $\varnothing D_{min}$ | 8 mm |
| Clamping height L_2 | 7.5 mm |
| Setting angle κ | 140 degrees |
| Insert size | 5 mm |
| ISO code toolholder | E08F SVOCR/L05 |
| Pack of insert screws | 269028 26 |
| Standard | Works standard |
| Application type | left-hand |
| Boring depth up to | 8xD |
| Tool material | Carbide |
| Through-coolant | yes |
| Application | Internal longitudinal turning |

Type of product

Boring bar