

Garant
GARANT Master Turn boring bar, steel spiral flutes, right-hand, Shank \varnothing / insert size: 25/16mm

Order data

Order number	261128 25/16
GTIN	4062406711085
Item class	21T

Technical description

Insert size	16 mm
Minimum pre-drill $\varnothing D_{\min}$	31 mm
Head length L_1	40 mm
Pack of insert screws	269028 8
Clamping height L_2	23 mm
Shank $\varnothing D_s$	25 mm
Setting angle κ	93 degrees
suitable indexable insert	VB.. 1604..
Overall length L	200 mm
Series	GARANT Master
ISO code toolholder	A25R SVUBR/L16
Centre offset L_3	17 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar