

Garant
GARANT Master Turn boring bar, steel spiral flutes, left-hand, Shank \varnothing / insert size: 20/11mm

Order data

Order number	260933 20/11
GTIN	4062406711054
Item class	21T

Technical description

Setting angle κ	90 degrees
Overall length L	200 mm
Insert size	11 mm
Shank \varnothing D _s	20 mm
ISO code toolholder	A20R STFCL/L11
Centre offset L ₃	11.1 mm
suitable indexable insert	TC.. 1102..
Series	GARANT Master
Minimum pre-drill \varnothing D _{min}	22 mm
Head length L ₁	36 mm
Clamping height L ₂	18 mm
Pack of insert screws	269028 7
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar