

Garant
GARANT Master Turn boring bar, steel spiral flutes, left-hand, Shank \varnothing / insert size: 16/11mm

Order data

Order number	261129 16/11
GTIN	4062406711092
Item class	21T

Technical description

ISO code toolholder	A16Q SVUBR/L11
Minimum pre-drill $\varnothing D_{\min}$	20 mm
Shank $\varnothing D_s$	16 mm
Pack of insert screws	269028 7
suitable indexable insert	VB.. 1103..
Centre offset L_3	11 mm
Series	GARANT Master
Head length L_1	31 mm
Insert size	11 mm
Overall length L	180 mm
Clamping height L_2	15 mm
Setting angle κ	93 degrees
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar